

Black Self-fusing Tape, 15 ft



Product Classification

Product Type Weatherproofing tape

Dimensions

Length 4.57 m | 15.00 ft
Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in
Width 38.10 mm | 1.50 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit Four 1/2 in–1/2 in | One 1/2 in–2-1/4 in | Two 1/2 in–7/8 in | Two 1/2 in–7/8 in to device
Color Black
Material Type Silicone tape
Ordering Note CommScope® non-standard product
Package Quantity 2

Mechanical Specifications

UV Resistance Test Method ASTM D518, Test Method B
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 8.3 cm | 3.3 in
Length 0.6 cm | 0.3 in
Shipping Weight 0.10 kg | 0.21 lb
Width 8.3 cm | 3.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

