



12 Port Entrance Panel, 3 x 4

Product Classification

Product Type Entrance panel

Dimensions

Height 647.70 mm | 25.50 in

Width 647.70 mm | 25.50 in

General Specifications

Number of Ports 12
Panel Type Multiple
Color Gray
Entry Panel Port Size 101.6 mm | 4.0 in
Includes Entry cap | Hardware | Port
Material Type Aluminum
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packed Dimensions

Height 698.5 mm | 27.5 in

Length 50.8 mm | 2.0 in

Shipping Weight 3.62 kg | 7.98 lb

Width 698.5 mm | 27.5 in

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

ISO 9001:2015
China RoHS SJ/T 11364-2014

Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)



Included Products

CAP-4 — Snap-in Entry Port Cap, 4 in