



24 Port Entrance Panel, 4 x 6

Product Classification

Product Type Entrance panel

Dimensions

Height 787.40 mm | 31.00 in
Width 1003.30 mm | 39.50 in

General Specifications

Number of Ports 24
Panel Type Multiple
Color Gray
Entry Panel Port Size 101.6 mm | 4.0 in
Includes Entry cap | Hardware | Port
Material Type Aluminum
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packed Dimensions

Height 668.0 mm | 26.3 in
Length 50.8 mm | 2.0 in
Shipping Weight 2.50 kg | 5.51 lb
Width 460.0 mm | 18.1 in

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)



Included Products

CAP-4 — Snap-in Entry Port Cap, 4 in



Snap-in Entry Port Cap, 4 in

Product Classification

Product Type Port cap

General Specifications

Panel Type Multiple
Color Black
Entry Panel Port Size 101.6 mm | 4.0 in
Includes Entry cap
Material Type Engineered plastic
Ordering Note CommScope® non-standard product
Package Quantity 1

Packed Dimensions

Height 127.0 mm | 5.0 in
Length 248.9 mm | 9.8 in
Shipping Weight 0.02 kg | 0.04 lb
Width 127.0 mm | 5.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

