



Boot Assembly, 4 in, for 1/4 in corrugated coaxial cable

OBSOLETE**Replaced By**

SEC-614

SnapSeal™ Entry Cushion with 6 holes for 1/4 in corrugated coaxial cable

Product Classification

Product Type	Boot assembly
---------------------	---------------

Dimensions

Nominal Size	1/4 in
Height	101.60 mm 4.00 in
Length	76.20 mm 3.00 in

General Specifications

Cable Type	Corrugated
Cables per Cushion	3
Color	Black
Includes	Boot Cushion Two clamps
Material Type	EPDM rubber
Ordering Note	CommScope® non-standard product
Package Quantity	1

Mechanical Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	≥1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packed Dimensions

Height	149.9 mm 5.9 in
---------------	-------------------

204679A-17

Length	79.8 mm 3.1 in
Shipping Weight	0.64 kg 1.42 lb
Width	149.9 mm 5.9 in