



Boot Assembly, 4 in, for 3/8 in corrugated coaxial cable

OBSOLETE**Replaced By**

SEC-638

SnapSeal™ Entry Cushion with 6 holes for 3/8 in corrugated coaxial cable

Product Classification

Product Type Boot assembly

Dimensions

Nominal Size 3/8 in
Height 101.60 mm | 4.00 in
Length 76.20 mm | 3.00 in

General Specifications

Cable Type Corrugated
Cables per Cushion 1
Color Black
Includes Boot | Cushion | Two clamps
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation ≥1000 hours
Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packed Dimensions

Height 149.9 mm | 5.9 in

204679A-19

Length	79.8 mm 3.1 in
Shipping Weight	0.64 kg 1.42 lb
Width	149.9 mm 5.9 in