



Boot Assembly, 4 in, for 3 in corrugated coaxial cable

## Product Classification

**Product Type** Boot assembly

## Dimensions

**Nominal Size** 3 in  
**Height** 101.60 mm | 4.00 in  
**Length** 76.20 mm | 3.00 in

## General Specifications

**Cable Type** Corrugated  
**Cables per Cushion** 1  
**Color** Black  
**Includes** Boot | Cushion | Two clamps  
**Material Type** EPDM rubber  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 1

## Mechanical Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 505  
**UV Resistance, minimum with no degradation** =1000 hours  
**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529:2001, IP66

## Packed Dimensions

**Height** 149.9 mm | 5.9 in  
**Length** 79.8 mm | 3.1 in  
**Shipping Weight** 0.64 kg | 1.42 lb  
**Width** 149.9 mm | 5.9 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

**Classification**

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

