



Cushion Insert with 3 holes for 1/2 in corrugated coaxial cable

Product Classification

Brand	I-Line
Product Type	Cushion insert

Dimensions

Nominal Size	1/2 in
Height	82.55 mm 3.25 in
Length	25.40 mm 1.00 in

General Specifications

Cable Type	Corrugated
Cables per Cushion	3
Color	Black
Includes	Cushion
Material Type	EPDM rubber
Ordering Note	CommScope® non-standard product
Package Quantity	1

Mechanical Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packed Dimensions

Height	169.9 mm 6.7 in
Length	99.8 mm 3.9 in
Shipping Weight	0.80 kg 1.76 lb
Width	129.8 mm 5.1 in