



Cushion Insert with 1 hole for 1-1/4 in corrugated coaxial cable

Product Classification

| | |
|---------------------|----------------|
| Brand | I-Line |
| Product Type | Cushion insert |

Dimensions

| | |
|---------------------|--------------------|
| Nominal Size | 1-1/4 in |
| Height | 82.55 mm 3.25 in |
| Length | 25.40 mm 1.00 in |

General Specifications

| | |
|---------------------------|---------------------------------|
| Cable Type | Corrugated |
| Cables per Cushion | 1 |
| Color | Black |
| Includes | Cushion |
| Material Type | EPDM rubber |
| Ordering Note | CommScope® non-standard product |
| Package Quantity | 1 |

Mechanical Specifications

| | |
|---|--|
| UV Resistance Test Method | MIL-STD-810E, Procedure 11, Method 505 |
| UV Resistance, minimum with no degradation | =1000 hours |
| Weather Resistance Test Method | 04AS00-03.9.0 IEC 60529:2001, IP66 |

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 169.9 mm 6.7 in |
| Length | 99.8 mm 3.9 in |
| Shipping Weight | 0.50 kg 1.10 lb |
| Width | 129.8 mm 5.1 in |