

Boot Assembly, 5 in, for 5/8 in corrugated coaxial cable



Product Classification

Product Type Boot assembly

Dimensions

Nominal Size 5/8 in
Height 127.00 mm | 5.00 in
Length 76.20 mm | 3.00 in

General Specifications

Cable Type Corrugated
Cables per Cushion 3
Color Black
Includes Boot | Cushion | Two clamps
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation =1000 hours
Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packed Dimensions

Height 190.5 mm | 7.5 in
Length 79.8 mm | 3.1 in
Shipping Weight 0.90 kg | 1.98 lb
Width 170.2 mm | 6.7 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

