

## Boot Assembly, 5 in, for 3/8 in corrugated coaxial cable



### Product Classification

**Product Type** Boot assembly

### Dimensions

**Nominal Size** 3/8 in  
**Height** 127.00 mm | 5.00 in  
**Length** 76.20 mm | 3.00 in

### General Specifications

**Cable Type** Corrugated  
**Cables per Cushion** 3  
**Color** Black  
**Includes** Boot | Cushion | Two clamps  
**Material Type** EPDM rubber  
**Ordering Note** CommScope® non-standard product  
**Package Quantity** 1

### Mechanical Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 505  
**UV Resistance, minimum with no degradation** =1000 hours  
**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529:2001, IP66

### Packed Dimensions

**Height** 190.5 mm | 7.5 in  
**Length** 79.8 mm | 3.1 in  
**Shipping Weight** 0.90 kg | 1.98 lb  
**Width** 170.2 mm | 6.7 in

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

**Classification**

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

