



Boot Assembly, 4 in

Product Classification

Brand	I-Line
Product Type	Boot assembly

Dimensions

Height	101.60 mm 4.00 in
Length	76.20 mm 3.00 in

General Specifications

Cable Type	Corrugated
Color	Black
Includes	Boot Two clamps
Material Type	EPDM rubber
Ordering Note	CommScope® non-standard product
Package Quantity	1

Mechanical Specifications

UV Resistance Test Method	MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation	=1000 hours
Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66

Packed Dimensions

Height	169.9 mm 6.7 in
Length	99.8 mm 3.9 in
Shipping Weight	0.80 kg 1.76 lb
Width	129.8 mm 5.1 in