



Universal Connector Grounding Kit for 1/2 in through 1-5/8 in corrugated coaxial cable

OBSOLETE

This product was discontinued on: October 1, 2013

Product Classification

Product Type Grounding kit

Dimensions

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 5/8 in | 7/8 in

Bonding Conductor Length 25.4 mm | 1 in

Cable Jacketing Removal Length, maximum 25.4 mm | 1 in

Cable Jacketing Removal Length, minimum 22.9 mm | 0.9 in

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Grounding Kit Type	Connector Grounding Kits
Cable Type	Corrugated
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa
Color	Black
Bonding Conductor Material	Copper
Bonding Conductor Jacketing Material	PVC
Grounding Strap Material	Stainless steel
Includes	M6 hardware One copper line tap One CTAP cover One grounding assembly One grounding clamp
Lug Attachment	Factory attached
Lug Type	Two-hole lug
Package Quantity	1

Mechanical Specifications

Thread Size M6

Packed Dimensions

Height 142.7 mm | 5.6 in

Length 79.0 mm | 3.1 in

Shipping Weight 3.45 kg | 7.61 lb

Width 142.7 mm | 5.6 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

