

Self-locking Hanger for 1/2 in RCT4 RADIAX® Radiating cable



Product Classification

Product Type Hanger kit

Dimensions

| | |
|-------------------------------------|----------------------|
| Nominal Size | 1/2 in |
| Compatible Diameter, maximum | 16.800 mm 0.661 in |
| Compatible Diameter, minimum | 14.300 mm 0.563 in |
| Height | 32.00 mm 1.26 in |
| Length | 20.60 mm 0.81 in |
| Width | 17.10 mm 0.67 in |

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

| | |
|-----------------------------|---------------------|
| Hanger Type | Self locking hanger |
| Cables per Hanger | 1 |
| Color | Black |
| Material Type | Polyamide PA12 |
| Maximum Stack Height | 2 |
| Package Quantity | 100 |

Mechanical Specifications

| | |
|---|--|
| Flammability Test Method | UL 94-HB |
| Maximum Load | 650 N 146 lbf |
| Toxicity Index Test Method | IEC 60754-2 |
| UV Resistance, minimum with no degradation | =500 hours exposure in accelerated UV life chamber |

209800-15B

Packed Dimensions

| | |
|------------------------|-------------------|
| Height | 10.0 cm 3.9 in |
| Length | 18.0 cm 7.1 in |
| Shipping Weight | 0.50 kg 1.10 lb |
| Width | 11.5 cm 4.5 in |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power