

209800-17B

Self-locking Hanger for 1/2 in RXL4 RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1/2 in
Compatible Diameter, maximum 19.500 mm | 0.768 in
Compatible Diameter, minimum 16.800 mm | 0.661 in
Height 35.40 mm | 1.39 in
Length 22.50 mm | 0.89 in
Width 19.50 mm | 0.77 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type Self locking hanger
Cables per Hanger 1
Color Black
Material Type Polyamide PA12
Maximum Stack Height 2
Package Quantity 100

Mechanical Specifications

Flammability Test Method UL 94-HB
Maximum Load 650 N | 146 lbf
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation =500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height 16.5 cm | 6.5 in
Length 19.0 cm | 7.5 in
Shipping Weight 0.70 kg | 1.54 lb
Width 11.0 cm | 4.3 in

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

*** Footnotes**

Maximum Stack Height Fiber, Hybrid, Power