

Self-locking Hanger for 7/8 in RXL5 RADIAX® Radiating cable



Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 7/8 in
Compatible Diameter, maximum 31.200 mm | 1.228 in
Compatible Diameter, minimum 27.800 mm | 1.094 in
Height 48.90 mm | 1.93 in
Length 33.40 mm | 1.31 in
Width 20.20 mm | 0.80 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type Self locking hanger
Cables per Hanger 1
Color Black
Material Type Polyamide PA12
Maximum Stack Height 2
Package Quantity 50

Mechanical Specifications

Flammability Test Method UL 94-HB
Maximum Load 850 N | 191 lbf
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation =500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height	19.0 cm 7.5 in
Length	16.5 cm 6.5 in
Shipping Weight	0.88 kg 1.94 lb
Width	11.0 cm 4.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power