



Self-locking Hanger for 1-1/4 in RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1-1/4 in
Compatible Diameter, maximum 39.500 mm | 1.555 in
Compatible Diameter, minimum 35.500 mm | 1.398 in
Height 59.40 mm | 2.34 in
Length 41.80 mm | 1.65 in
Width 21.00 mm | 0.83 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type Self locking hanger
Cables per Hanger 1
Color Black
Material Type Polyamide PA12
Maximum Stack Height 2
Package Quantity 50

Mechanical Specifications

Flammability Test Method UL 94-HB
Maximum Load 1200 N | 270 lbf
Toxicity Index Test Method IEC 60754-2
UV Resistance, minimum with no degradation =500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height	11.5 cm 4.5 in
Length	25.0 cm 9.8 in
Shipping Weight	1.12 kg 2.47 lb
Width	14.5 cm 5.7 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power