



Self-locking Hanger for 1-5/8 in RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size	1-5/8 in
Compatible Diameter, maximum	50.500 mm 1.988 in
Compatible Diameter, minimum	46.500 mm 1.831 in
Height	72.80 mm 2.87 in
Length	53.50 mm 2.11 in
Width	22.00 mm 0.87 in

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

General Specifications

Hanger Type	Self locking hanger
Cables per Hanger	1
Color	Black
Material Type	Polyamide PA12
Maximum Stack Height	2
Package Quantity	25

Mechanical Specifications

Flammability Test Method	UL 94-HB
Maximum Load	1400 N 315 lbf
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	=500 hours exposure in accelerated UV life chamber

Packed Dimensions

Height	11.5 cm 4.5 in
Length	30.0 cm 11.8 in
Shipping Weight	2.10 kg 4.63 lb
Width	8.5 cm 3.3 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power