



## Messenger Wire Tie Wrap with spacer for RCT RADIAX® Radiating cable

- For added support, use with Andrew Stainless Steel Cable Ties (250058) at 5 meter intervals

### Product Classification

**Product Type** Wire tie

### Dimensions

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in  
**Compatible Diameter, maximum** 114.000 mm | 4.488 in  
**Height** 25.40 mm | 1.00 in  
**Length** 406.00 mm | 15.98 in  
**Width** 12.70 mm | 0.50 in

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

### General Specifications

**Hanger Type** Cable tie  
**Cables per Hanger** 1  
**Color** Black  
**Material Type** Engineered plastic  
**Package Quantity** 1

### Mechanical Specifications

**Flammability Test Method** UL 94-HB  
**Mounting** Messenger wire  
**Pullout Force, maximum with no cable slippage** 445 N | 100 lbf  
**UV Resistance, minimum with no degradation** =100 hours exposure in accelerated UV life chamber

### Packed Dimensions

**Shipping Weight** 0.02 kg | 0.03 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

