

Universal Snap-in Hanger for 2-1/4 in corrugated coaxial cable



OBSOLETE

Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 2-1/4 in
Compatible Diameter, maximum 52.070 mm | 2.050 in
Compatible Diameter, minimum 48.260 mm | 1.900 in
Height 41.00 mm | 1.61 in
Length 90.00 mm | 3.54 in
Width 60.00 mm | 2.36 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Snap-in hanger
Cable Type Corrugated
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Ordering Note CommScope® non-standard product
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	3/8 in (M10) drilled cable ladder
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	17.0 cm 6.7 in
Length	10.0 cm 3.9 in
Shipping Weight	0.71 kg 1.57 lb
Width	13.0 cm 5.1 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

