

## Universal Snap-in Hanger for 5/8 in corrugated coaxial cable



### **OBSOLETE**

This product was discontinued on: **December 31, 2018**

### **Replaced By**

SSH-M

SnapStak® Plus Adjustable Hanger for 14mm to 25mm Cable - No Grommets Required. For patents, see [www.cs-pat.com](http://www.cs-pat.com).

## Product Classification

**Product Type** Hanger kit

## Dimensions

<b>Nominal Size</b>	5/8 in
<b>Compatible Diameter, maximum</b>	22.022 mm   0.867 in
<b>Compatible Diameter, minimum</b>	20.828 mm   0.820 in
<b>Height</b>	41.00 mm   1.61 in
<b>Length</b>	56.00 mm   2.20 in
<b>Width</b>	36.30 mm   1.43 in

## Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Hanger Type</b>	Snap-in hanger
<b>Cable Type</b>	Corrugated
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver

# 206706A-6

---

<b>Material Type</b>	Stainless steel
<b>Ordering Note</b>	CommScope® non-standard product
<b>Package Quantity</b>	10

## Mechanical Specifications

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Mounting</b>	3/4 in through hole
<b>Vibration Survival</b>	≥4 hours at resonant frequency
<b>Environmental Strength Capability</b>	Double cable weight

## Packed Dimensions

<b>Height</b>	17.0 cm   6.7 in
<b>Length</b>	10.0 cm   3.9 in
<b>Shipping Weight</b>	0.35 kg   0.78 lb
<b>Width</b>	13.0 cm   5.1 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

