

## Butterfly Hanger for elliptical waveguide 17



## Product Classification

**Product Type** Hanger kit

## Dimensions

**Height** 76.20 mm | 3.00 in

**Waveguide Size** EW17

## Electrical Specifications

**DTF Effect** 0.1 dB

**Return Loss Effect** 0.1 dB

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

**Hanger Type** Standard butterfly hanger

**Cable Type** Elliptical waveguide

**Cables per Hanger** 1

**Color** Silver

**Material Type** Stainless steel

**Ordering Note** CommScope® non-standard product

**Package Quantity** 10

## Mechanical Specifications

**Corrosion Resistance, minimum with no degradation** =500 hours in salt spray chamber

**Mounting** 3/8 in (M10) drilled cable ladder

**Vibration Survival** =4 hours at resonant frequency

**Environmental Strength Capability** Double cable weight

## Packed Dimensions

# 31766A-9

---

<b>Height</b>	47.0 cm   18.5 in
<b>Length</b>	10.8 cm   4.3 in
<b>Shipping Weight</b>	2.23 kg   4.92 lb
<b>Width</b>	10.8 cm   4.3 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

