

Universal Snap-in Hanger for elliptical waveguide 240



Product Classification

Product Type Hanger kit

Dimensions

Height 41.00 mm | 1.61 in
Length 73.00 mm | 2.87 in
Waveguide Size WR42 | WG20 | R220
Width 43.00 mm | 1.69 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Snap-in hanger
Cable Type Elliptical waveguide
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Package Quantity 10

Mechanical Specifications

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber
Mounting 3/4 in through hole
Vibration Survival ≥4 hours at resonant frequency
Environmental Strength Capability Double cable weight

EWSH-240

Packed Dimensions

Height	20.0 cm 7.9 in
Length	20.0 cm 7.9 in
Shipping Weight	1.60 kg 3.53 lb
Width	20.0 cm 7.9 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

