



Lace-up Hoisting Grip for 4 in coaxial cable and elliptical waveguide 17 and 20

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 4 in
Grip Length, minimum 965.20 mm | 38.00 in
Leader Length, minimum 508.00 mm | 20.00 in
Waveguide Size WR430 | WG8 | R22

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Cable Type Corrugated | Elliptical waveguide
Material Type Tin-coated bronze
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 500 lb

Packed Dimensions

Shipping Weight 1.56 kg | 3.44 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

