



Single Entrance Panel for elliptical waveguide 37

Product Classification

Product Type Entrance panel

Dimensions

Height 76.20 mm | 3.00 in
Waveguide Size WR229 | WG11 | R40
Width 127.00 mm | 5.00 in

General Specifications

Number of Ports 1
Panel Type Single
Color Gray
Entry Panel Port Size 101.6 mm | 4.0 in
Includes Boot | Plate
Material Type Aluminum
Package Quantity 1

Mechanical Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529.14.2

Packed Dimensions

Height 180.0 mm | 7.1 in
Length 180.0 mm | 7.1 in
Shipping Weight 0.91 kg | 2.01 lb
Width 180.0 mm | 7.1 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

204673-1 — 1 Port Entrance Panel 1 x 1

- CAP-4 — Snap-in Entry Port Cap, 4 in

WGB4-37 — Boot Assembly, 4 in, for elliptical waveguide 37