

Quik-V Sector Frame, 14 ft face, pipe ordered separately



Product Classification

Product Type Tower sector frame

Dimensions

Face Width 4.4 m | 14.5 ft
Height 1041.4 mm | 41.0 in
Length 863.6 mm | 34.0 in
Mounting Diameter, maximum 203.2 mm | 8 in
Mounting Diameter, minimum 0.0 mm | 0 in
Weight 197.4 kg | 435.2 lb
Width 4419.6 mm | 174.0 in

Environmental Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL
Wind Rating Test Method TIA/EIA-222

General Specifications

Pipe, quantity 0
Stand-off Distance 863.6 mm | 34.0 in
Tower Taper Non-tapered | Tapered
Includes Clamps | Frame | Saddle mounts | Stiff arm
Material Type Hot dip galvanized steel
Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD
Package Quantity 1

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code