



Single Entrance Panel for elliptical waveguide 63

## Product Classification

**Product Type** Entrance panel

## Dimensions

**Height** 76.20 mm | 3.00 in  
**Waveguide Size** WR137 | WG14 | R70  
**Width** 127.00 mm | 5.00 in

## General Specifications

**Number of Ports** 1  
**Panel Type** Single  
**Color** Gray  
**Entry Panel Port Size** 101.6 mm | 4.0 in  
**Includes** Boot | Plate  
**Material Type** Aluminum  
**Package Quantity** 1

## Mechanical Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

## Packed Dimensions

**Height** 180.0 mm | 7.1 in  
**Length** 180.0 mm | 7.1 in  
**Shipping Weight** 0.91 kg | 2.01 lb  
**Width** 180.0 mm | 7.1 in

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

204673-1 — 1 Port Entrance Panel 1 x 1

- CAP-4 — Snap-in Entry Port Cap, 4 in

WGB4-63 — Boot Assembly, 4 in, for elliptical waveguide 63