

LUHG-38



HELIAX® FiberFeed® Discrete trunk Lace-up Hoisting Grip for all RFFT series cables

Product Classification

Brand FiberFeed® | HELIAX®

Product Type Hoisting grip

Dimensions

Nominal Size 3/8 in

Grip Length, minimum 152.40 mm | 6.00 in

Leader Length, minimum 165.10 mm | 6.50 in

Electrical Specifications

DTF Effect 0.1 dB

Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip

Attachment Spacing Intervals 61 m | 200 ft

Installation Tool Required; not included

Material Type Stainless steel

Ordering Note CommScope® non-standard product

Package Quantity 1

Support Clamp Not included

Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 200 lb

Packed Dimensions

Height 5.7 cm | 2.3 in

Length 26.7 cm | 10.5 in

Width 26.7 cm | 10.5 in

Shipping Weight 0.04 kg | 0.09 lb