



Cushion Plugs for 1-5/8 in coaxial cable

OBSOLETE

This product was discontinued on: January 1, 2009

Replaced By

PLUG-158 Cushion Plugs for 1-5/8 in corrugated coaxial cable

Product Classification

Product Type Cushion plug

Dimensions

Length 50.80 mm | 2.00 in

General Specifications

Cable Type Corrugated
Accessories Boot Assemblies
Color Black
Includes Five plugs
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 5

Mechanical Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505
UV Resistance, minimum with no degradation ≥1000 hours
Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packed Dimensions

Height 304.8 mm | 12.0 in
Length 50.8 mm | 2.0 in

1873-CP

Shipping Weight

0.30 kg | 0.66 lb

Width

279.4 mm | 11.0 in