



Angle Adapter, compact 1/4 in tapped hole

Product Classification

Product Type Adapter

Dimensions

Inside Length 16.00 mm | 0.63 in
Inside Width 16.51 mm | 0.65 in
Outside Length 44.45 mm | 1.75 in
Outside Width 21.59 mm | 0.85 in

General Specifications

Adapter Type Angle adapter
Material Type Zinc-plated steel
Ordering Note CommScope® non-standard product
Package Quantity 10

Mechanical Specifications

Installation Torque, maximum 12.0 ft lb
Installation Torque, minimum 10.0 ft lb
Material Thickness 2.337 mm | 0.092 in
Maximum Loading Single, 1-5/8 in cable
Mounting 1/4 in tapped hole

Packed Dimensions

Height 2.5 cm | 1.0 in
Length 20.3 cm | 8.0 in
Shipping Weight 0.69 kg | 1.52 lb
Width 12.7 cm | 5.0 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

