



Fiber Breakout Kit, outside plant cable

Product Classification

Portfolio	SYSTIMAX®
Product Type	Fiber breakout kit, rectangular
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Material Type, body	Acrylonitrile butadiene styrene (ABS)
Material Type, tubing	PVC

Dimensions

Tube Inner Diameter	500.00 µm
Tube Outer Diameter	900.00 µm

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

General Specifications

Application	Buffers approximately 100 fibers
Color	Black
Compatible Interface	LC LC, keyed SC ST
Includes	Buffer tubing, 900 micron, 210 ft Clear PVC tubing, 1 ft, 0.234 in ID Clear PVC tubing, 2 ft, 0.166 in ID Clear PVC tubing, 25 ft, 0.095 in ID Eight unit splitter with clear cover Five syringes with applicator tip Heat shrink tubing, 2 ft, 0.187 in ID Instruction sheet Rosin bag Six clear PVC tubes, 2 in, 0.294 in ID Six unit splitter with clear cover Wire marker book
Ordering Note	Order B sealant separately
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

