



6-to-1 Unit Splitter, for 0.16 in and 0.20 in core tubes

Product Classification

Portfolio	SYSTIMAX®
Product Type	Unit splitter kit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Material Type, body	Acrylonitrile butadiene styrene (ABS)
----------------------------	---------------------------------------

Dimensions

Height	8.13 mm 0.32 in
Length	50.80 mm 2.00 in
Width	20.32 mm 0.80 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

General Specifications

Color	Black
Compatible Interface	LC LC, keyed SC ST
Includes	Six unit splitter Split tube seal Syringe
Ordering Note	Order B sealant separately
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

