



2 x 12 Fiber Breakout Kit, outside plant cable, gel blocking

Product Classification

Portfolio	SYSTIMAX®
Product Type	Fiber breakout kit, rectangular
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Material Type, body	Acrylonitrile butadiene styrene (ABS)
Material Type, tubing	PVC Thermoplastic elastomer (TPE)

Dimensions

Height	7.62 mm 0.30 in
Length	43.18 mm 1.70 in
Tube Inner Diameter	500.00 µm
Tube Outer Diameter	900.00 µm
Width	17.78 mm 0.70 in

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Color	Black Clear
Compatible Interface	LC LC, keyed SC ST
Includes	Instruction sheet Talc bag Ten cable ties Twenty-five feet white PVC tubing, .095 in inner diameter Two breakout units, twelve 24 in x 900 µm buffer tubing each Two clear flexible plastic tubes Two splitter kits with talc bag Two syringe tips Two syringes
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

