



Messenger Stainless Steel Cable Tie for RCT RADIAX® Radiating cables

Product Classification

Product Type Cable tie

Dimensions

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in
Compatible Diameter, maximum 102.000 mm | 4.016 in
Height 5.10 mm | 0.20 in
Length 362.00 mm | 14.25 in
Width 7.90 mm | 0.31 in

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Cable tie
Cables per Hanger 1
Material Type Stainless steel
Package Quantity 1

Mechanical Specifications

Flammability Test Method UL 2043
Mounting Messenger wire
Pullout Force, maximum with no cable slippage 700 N | 157 lbf

Packed Dimensions

Shipping Weight 0.01 kg | 0.02 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

