



6 Fiber Breakout Kit, loose tube

## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber breakout kit, rectangular
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Material Type, body</b>	Acrylonitrile butadiene styrene (ABS)
<b>Material Type, tubing</b>	Thermoplastic elastomer (TPE)

## Dimensions

<b>Height</b>	7.62 mm   0.30 in
<b>Length</b>	43.18 mm   1.70 in
<b>Tube Inner Diameter</b>	500.00 µm
<b>Tube Length</b>	609.6 mm   24.0 in
<b>Tube Outer Diameter</b>	900.00 µm
<b>Width</b>	17.78 mm   0.70 in

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

## General Specifications

<b>Color</b>	Black
<b>Compatible Interface</b>	LC   LC, keyed   SC   ST
<b>Includes</b>	Breakout unit   Instruction sheet   Six buffer tubes, 24 in x 900 µm   Snap together housing
<b>Package Quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

