



12 Fiber Breakout Kit, loose tube

Product Classification

Portfolio	SYSTIMAX®
Product Type	Fiber breakout kit, rectangular
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Material Type, body	Acrylonitrile butadiene styrene (ABS)
Material Type, tubing	Thermoplastic elastomer (TPE)

Dimensions

Height	7.62 mm 0.30 in
Length	43.18 mm 1.70 in
Tube Inner Diameter	500.00 µm
Tube Length	609.6 mm 24.0 in
Tube Outer Diameter	900.00 µm
Width	17.78 mm 0.70 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
------------------------------	--------------------------------------

General Specifications

Color	Black
Compatible Interface	LC LC, keyed SC ST
Includes	Breakout unit Instruction sheet Snap together housing Twelve buffer tubes, 24 in x 900 µm
Package Quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

