



Flex-Twist Hanger Assembly for WR137

Product Classification

Product Type Hanger kit

Dimensions

Waveguide Size WR137 | WG14 | R70

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Flex-Twist hanger
Cable Type Elliptical waveguide
Cables per Hanger 1
Color Silver
Includes Clamp | Rubber grommet | Threaded rod
Material Type Stainless steel
Package Quantity 1

Mechanical Specifications

Corrosion Test Method MIL-STD-889B | MIL-F-14072C
Mounting 4.5 in OD pipe
Wind Velocity Survival Rating with 1/2 in (12 mm) Radial Ice 201 km/h | 125 mph

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

