



Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter

OBSOLETE

This product was discontinued on: April 1, 2014

Product Classification

Brand	ValuSite™
Product Type	Hanger kit

Dimensions

Nominal Size	1-1/4 in
Compatible Diameter, maximum	40.132 mm 1.580 in
Compatible Diameter, minimum	38.100 mm 1.500 in
Height	184.32 mm 7.26 in
Length	120.46 mm 4.74 in
Width	25.89 mm 1.02 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Composite clamp
Cables per Hanger	6
Color	Black
Includes	Angle adapter Hardware

DHK-114-6-P

Material Type	Engineered plastic Stainless steel
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa
Package Quantity	1

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Mounting	M8 hardware
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Vibration Survival	≥4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	31.8 cm 12.5 in
Length	7.6 cm 3.0 in
Shipping Weight	0.48 kg 1.06 lb
Width	31.8 cm 12.5 in

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power