



Cold shrink Kit for 1/2 in through 3/8 in cable to 1/2 in through 3/8 in cable

Product Classification

Product Type Cold shrink kit

Dimensions

Nominal Size 1/2 in | 3/8 in
Cable Diameter for Seal, maximum 21.34 mm | 0.84 in
Cable Diameter for Seal, minimum 7.37 mm | 0.29 in
Inner Diameter 53.09 mm | 2.09 in
Length 202.95 mm | 7.99 in

General Specifications

Application Provides additional moisture seal for cable connections
Applications per Kit One 1/2 in–3/8 in to 1/2 in–3/8 in
Color Black
Includes One EPDM rubber tube | One sealing foam strip
Material Type EPDM rubber
Ordering Note CommScope® non-standard product
Package Quantity 1

Mechanical Specifications

UV Resistance Test Method UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp
UV Resistance, minimum with no degradation =1000 hours
Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 30.0 cm | 11.8 in
Length 7.6 cm | 3.0 in
Shipping Weight 0.14 kg | 0.30 lb
Width 7.6 cm | 3.0 in

Regulatory Compliance/Certifications

Agency **Classification**

245173

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

