

CH-1-14-85M-KT-25



Metal Hanger Kit for 1-1/4 in RADIAX® Radiating cable, Standoff included

Product Classification

Brand RADIAX®
Product Type Hanger kit

Dimensions

Nominal Size 1-1/4 in

Environmental Specifications

Operating Temperature -30 °C to +80 °C (-22 °F to +176 °F)

General Specifications

Hanger Type Hanger kits
Accessories Hangers
Cable Type Smoothwall
Cables per Hanger 1
Color Silver
Material Type Stainless steel
Maximum Stack Height 1
Ordering Note CommScope® non-standard product
Package Quantity 25

Mechanical Specifications

Hanger Spacing, maximum 1.3 m | 4.3 ft

Packed Dimensions

Height 170.0 mm | 6.7 in
Length 375.0 mm | 14.8 in
Shipping Weight 4.10 kg | 9.04 lb
Width 230.0 mm | 9.1 in

* Footnotes

CH-1-14-85M-KT-25

Maximum Stack Height Fiber, Hybrid, Power