

252026-10KT-P

Angle Adapter, miniature, (5/16") tapped hole



Product Classification

Product Type Adapter

Dimensions

Inside Length 12.70 mm | 0.50 in
Inside Width 15.88 mm | 0.63 in
Outside Length 29.97 mm | 1.18 in
Outside Width 25.40 mm | 1.00 in

General Specifications

Adapter Type Angle adapter

Material Type Stainless steel 304

Ordering Note CommScope® standard product in Europe, the Middle East, and Africa | CommScope® standard product in Mexico, Central America, and South America | CommScope® standard product in the United States and Canada

Package Quantity 10

Mechanical Specifications

Installation Torque, maximum 13.0 ft lb

Installation Torque, minimum 11.0 ft lb

Material Thickness 14.224 mm | 0.560 in

Maximum Loading Triple stack, 1/2 in cable

Packed Dimensions

Height 11.3 cm | 4.4 in

Length 6.0 cm | 2.4 in

Shipping Weight 0.85 kg | 1.87 lb

Width 10.0 cm | 3.9 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

Below Maximum Concentration Value (MCV)

