



Lace-up Hoisting Grip with tie wraps for HELIAX® FiberFeed® cables

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 1-1/4 in
Grip Length, minimum 635.00 mm | 25.00 in
Leader Length, minimum 203.20 mm | 8.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Material Type Stainless steel
Ordering Note CommScope® non-standard product
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 900 lb

Packed Dimensions

Height 5.7 cm | 2.3 in
Length 23.5 cm | 9.3 in
Width 23.5 cm | 9.3 in
Shipping Weight 0.38 kg | 0.83 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)

