

# ST-SVPBH20

---



## Solar/Video Hinged Based Communication Pole, 20 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

## Product Classification

**Product Type** Monopole

## Dimensions

**Height** 6.1 m | 20.0 ft  
**Mounting Diameter, maximum** 139.7 mm | 5 1/2 in  
**Mounting Diameter, minimum** 76.2 mm | 3 in  
**Weight** 146.4 kg | 322.7 lb

## Environmental Specifications

**Wind Rating Test Method** TIA/EIA-222-G

## General Specifications

**Foundation** Base  
**Monopole Capability Type** Light duty  
**Application** Solar | Supervisory Control and Data Acquisition (SCADA)/Video surveillance  
**Equipment Load Rating** Omni antenna | Solar panel | Telecommunications unit  
**Includes** Ground tab | Hand holes | Lightning rod | Monopole  
**Material Type** Hot dip galvanized steel  
**Monopole Design** Round conical  
**Optional Accessories** Antenna mounts | Cabinet mounts | Helical base foundation | Solar mounts | Video mounts  
**Package Quantity** 1