

ST-SVP20



Solar/Video Embedded Communication Pole, 20 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

Product Classification

Product Type Monopole

Dimensions

Height 6.1 m | 20.0 ft
Mounting Diameter, maximum 162.6 mm | 6.4 in
Mounting Diameter, minimum 76.2 mm | 3 in
Weight 69.3 kg | 152.9 lb

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Embedded
Monopole Capability Type Light duty
Application Solar | Supervisory Control and Data Acquisition (SCADA)/Video surveillance
Equipment Load Rating Omni antenna | Solar panel | Telecommunications unit
Includes Ground tab | Hand holes | Lightning rod | Monopole
Material Type Hot dip galvanized steel
Monopole Design Round conical
Optional Accessories Antenna mounts | Ballast mounting kit | Cabinet mounts | Solar mounts | Video mounts
Package Quantity 1