

# ST-SVP40

---



## Solar/Video Embedded Communication Pole, 40 ft

- Hinged design
- No climbing necessary for equipment installation
- Single person service
- Secure locking

## Product Classification

**Product Type** Monopole

## Dimensions

**Height** 12.2 m | 40.0 ft  
**Mounting Diameter, maximum** 276.9 mm | 10.9 in  
**Mounting Diameter, minimum** 114.3 mm | 4 1/2 in  
**Weight** 211.1 kg | 465.5 lb

## Environmental Specifications

**Wind Rating Test Method** TIA/EIA-222-G

## General Specifications

**Foundation** Embedded  
**Monopole Capability Type** Light duty  
**Application** Solar | Supervisory Control and Data Acquisition (SCADA)/Video surveillance  
**Equipment Load Rating** Omni antenna | Solar panel | Telecommunications unit  
**Includes** Ground tab | Hand holes | Lightning rod | Monopole  
**Material Type** Hot dip galvanized steel  
**Monopole Design** Round conical  
**Optional Accessories** Antenna mounts | Ballast mounting kit | Cabinet mounts | Solar mounts | Video mounts  
**Package Quantity** 1