



SlimLine Concealment Monopole, 40 ft with 20 ft radome

- Improved aesthetics with concealment design

Product Classification

Product Type Monopole

Dimensions

Height 12.2 m | 40.0 ft

Radome Height 6.1 m | 20.0 ft

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Base

Monopole Capability Type Heavy duty

Application Multi-carrier, multi sided monopole

Includes Ground tab | Hand holes | Monopole | Shroud

Material Type Hot dip galvanized steel

Monopole Design Multi-sided

Optional Accessories Antenna mounts | Foundation | Lightning rod

Package Quantity 1