

ST-EOG30



Embedded Oil and Gas, Energy, and Utility Pole, 30 ft

- Quick deploy embedment
- Collar mounting

Product Classification

Product Type Monopole

Dimensions

Height 18.3 m | 60.0 ft

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Embedded

Monopole Capability Type Medium duty

Application Multi-point telecommunications | Point-to-point communications

Equipment Load Rating 18 in microwave reflector | Omni antenna | Telecommunications unit

Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs

Material Type Hot dip galvanized steel

Monopole Design Round conical

Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts

Package Quantity 1