

ST-EOG40



Embedded Oil and Gas, Energy, and Utility Pole, 40 ft

- Quick deploy embedment
- Collar mounting

Product Classification

Product Type Monopole

Dimensions

Height 12.2 m | 40.0 ft
Mounting Diameter, maximum 274.6 mm | 10.8 in
Mounting Diameter, minimum 127.0 mm | 5 in
Weight 353.8 kg | 780.0 lb

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Embedded
Monopole Capability Type Medium duty
Application Multi-point telecommunications | Point-to-point communications
Equipment Load Rating 18 in microwave reflector | Omni antenna | Telecommunications unit
Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs
Material Type Hot dip galvanized steel
Monopole Design Round conical
Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts
Package Quantity 1