

# ST-FBP40

---



Embedded Oil and Gas, Energy, and Utility Pole, 40 ft

- Quick deploy embedment
- Collar mounting

## Product Classification

**Product Type** Monopole

## Dimensions

**Height** 12.2 m | 40.0 ft  
**Mounting Diameter, maximum** 304.8 mm | 12 in  
**Mounting Diameter, minimum** 160.0 mm | 6.3 in  
**Weight** 405.1 kg | 893.0 lb

## Environmental Specifications

**Wind Rating Test Method** TIA/EIA-222-G

## General Specifications

**Foundation** Base  
**Monopole Capability Type** Medium duty  
**Application** Multi-point telecommunications | Point-to-point communications  
**Equipment Load Rating** 18 in microwave reflector | Omni antenna | Telecommunications unit  
**Includes** Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs  
**Material Type** Hot dip galvanized steel  
**Monopole Design** Round conical  
**Optional Accessories** Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts  
**Package Quantity** 1