

ST-FBP50



Embedded Oil and Gas, Energy, and Utility Pole, 50 ft

- Quick deploy embedment
- Collar mounting

Product Classification

Product Type Monopole

Dimensions

Height 15.2 m | 50.0 ft
Mounting Diameter, maximum 266.7 mm | 10 1/2 in
Mounting Diameter, minimum 101.6 mm | 4 in
Weight 418.5 kg | 922.6 lb

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Base
Monopole Capability Type Medium duty
Application Multi-point telecommunications | Point-to-point communications
Equipment Load Rating 18 in microwave reflector | Omni antenna | Telecommunications unit
Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs
Material Type Hot dip galvanized steel
Monopole Design Round conical
Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts
Package Quantity 1