

ST-ERR60



Embedded Railroad Pole, 60 ft

- Quick deploy embedment
- Rivet nut mounting

Product Classification

Product Type Monopole

Dimensions

Height 18.3 m | 60.0 ft

Environmental Specifications

Wind Rating Test Method TIA/EIA-222-G

General Specifications

Foundation Embedded

Monopole Capability Type Medium duty

Application Positive train control/Centralized traffic control (PTC/CTC communications)

Equipment Load Rating 24 in microwave reflector | Directional antenna | Telecommunications unit | Yagi antenna

Includes Ground tab | Hand holes | Lightning rod | Monopole | Safety-climb | Step pegs

Material Type Hot dip galvanized steel

Monopole Design Multi-sided

Optional Accessories Antenna mounts | Cabinet mounts | Removable step pegs | Solar mounts

Package Quantity 1